

# 760253088 | OCM8-SP124LLG-40DB



OCM8 Fiber Optic Splitter Module, Planar, 2x4 Splitter, singlemode, LC/APC, symmetrical split ratio, 4 m pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   EMEA   India   Latin America   North America
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM8

## General Specifications

<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Distribution Type</b>	2 x 4 splitter
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	5 mm   0.197 in
<b>Depth</b>	45 mm   1.772 in
<b>Length</b>	100 mm   3.937 in
<b>Pigtail Length, Input</b>	4 m   13.123 ft
<b>Pigtail Length, Output</b>	4 m   13.123 ft
<b>Pigtail Diameter, Input</b>	1.8 mm   0.071 in
<b>Pigtail Diameter, Output</b>	1.8 mm   0.071 in

## Optical Specifications

<b>Fiber Type</b>	G.657.A1
<b>Directivity, minimum</b>	55 dB
<b>Polarization Dependent Loss, maximum</b>	0.3 dB
<b>Uniformity, maximum</b>	1.65 dB
<b>Wavelength Range</b>	1260–1650 nm

# 760253088 | OCM8-SP124LLG-40DB

---

<b>Insertion Loss, Splitter, maximum</b>	8 dB
<b>Return Loss, Connector, minimum</b>	55 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

