760253092 | OCM8-SP12GLLG-40DB



OCM8 Fiber Optic Splitter Module, Planar, 2x16 Splitter, singlemode, LC /APC, symmetrical split ratio, 4 m pigtails

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Europe | India | Latin America | North America

Product Type Splitter module

Product Series OCM8

General Specifications

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Distribution Type 2 x 16 splitter

Interface, InputLC/APCInterface, OutputLC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

Pigtail Length, Input4 m | 13.123 ftPigtail Length, Output4 m | 13.123 ftPigtail Diameter, Input1.8 mm | 0.071 inPigtail Diameter, Output1.8 mm | 0.071 in

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

COMMSCOPE®

760253092 | OCM8-SP12GLLG-40DB

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

