FBPS-LGX-4RU-BLK



LGX Fiber Chassis, 4RU, 19-inch or 23-inch, back to back, maximum capacity 28 single-width LGX modules or 14 dual-width LGX modules

The LGX 4RU back-to-back chassis holds 14 single-width LGX modules per side or seven dual-width LGX modules per side

Maximum shelf density of 28 single-width LGX modules or 14 dual-width LGX modul

2.5-in., 5-in., or 8-in. recess mounting options available

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch chassis

Product Series LSX

General Specifications

Color Black

Interface, front Unloaded

Rack Units 4

Dimensions

 Height
 175.25 mm | 6.9 in

 Width
 431.8 mm | 17 in

 Depth
 381 mm | 15 in

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (-40 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity

