_X1SSP1102006 | LGX SPLTR MOD (6) 1X2 APC/LC



Single width LGX module, 1x2 symmetrical split ratio, 6 splitters, LC/APC connectors

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117-58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Splitter module **Product Type**

LGX **Product Series**

Build America Buy America (BABA) compliant* **Government Requirements**

General Specifications

Functionality Splitting

Planar lightwave circuit (PLC) **Technology Type**

Distribution Type 1 x 2 splitter Interface, Input LC/APC

Interface, Output LC/APC

Location of Manufacturing Waived per BABA waiver for BEAD Program

Split Ratio Symmetrical

Splitter, quantity

Dimensions

Height 130.05 mm | 5.12 in Width 28.7 mm | 1.13 in Length

Optical Specifications

Directivity, minimum 55 dB 0.2 dB Polarization Dependent Loss, maximum

COMMSCOPE®

127 mm | 5 in

LX1SSP1102006 | LGX SPLTR MOD (6) 1X2 APC/LC

Uniformity, maximum 0.85 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum4.2 dBReturn Loss, Splitter, minimum50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1

