## LX1SSP1116001 | LGX SPLTR MOD 1X16 APC/LC



Single width LGX module, 1x16 symmetrical split ratio, 1 splitter, LC/APC connectors

 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

**Product Type** Splitter module

Product Series LGX

**Government Requirements**Build America Buy America (BABA) compliant\*

General Specifications

**Functionality** Splitting

**Technology Type**Planar lightwave circuit (PLC)

**Distribution Type** 1 x 16 splitter

Interface, InputLC/APCInterface, OutputLC/APC

**Location of Manufacturing** Waived per BABA waiver for BEAD Program

Split Ratio Symmetrical

Splitter, quantity 1

**Dimensions** 

 Height
 130.05 mm | 5.12 in

 Width
 28.7 mm | 1.13 in

 Length
 127 mm | 5 in

**Optical Specifications** 

Directivity, minimum55 dBPolarization Dependent Loss, maximum0.3 dB



## LX1SSP1116001 | LGX SPLTR MOD 1X16 APC/LC

Uniformity, maximum 1.55 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum14.2 dBReturn Loss, Splitter, minimum50 dB

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1

