LX1SSP4108001 | LGX SPLTR MOD 1X8 UPC/SC



Single width LGX module, 1x8 symmetrical split ratio, 1 splitter, SC/UPC connectors

*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Splitter module

Product Series LGX

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Functionality Splitting

Technology TypePlanar lightwave circuit (PLC)

Distribution Type1 x 8 splitterInterface, InputSC/UPC

Interface, Output SC/UPC

Location of ManufacturingWaived per BABA waiver for BEAD Program

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 130.05 mm | 5.12 in

 Width
 28.7 mm | 1.13 in

 Length
 127 mm | 5 in

Optical Specifications

Directivity, minimum55 dBPolarization Dependent Loss, maximum0.2 dB



LX1SSP4108001 | LGX SPLTR MOD 1X8 UPC/SC

Uniformity, maximum 1.3 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum10.9 dBReturn Loss, Splitter, minimum50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1

