760252359 | PPL-AP-8-LC-SM



Propel pass-through adapter pack, singlemode, 4 duplex LC/UPC ports

- Can be installed and removed from front or rear of panel
- QR code provides easy access to product documentation
- 8f, 12f, 16f or 24f sizes are interchangeable within Propel panels or blades
- This component requires 2 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber adapter pack

Product Brand Propel
Product Series PPL

General Specifications

Adapter Color Blue Interface LC/UPC

Interface Feature Dust caps | Internal shutters

Total Ports, quantity 4

Dimensions

 Height
 11 mm | 0.433 in

 Width
 65 mm | 2.559 in

 Depth
 170 mm | 6.693 in

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Safety Standard c-UL-us

Packaging and Weights

Packaging quantity

COMMSCOPE®

760252359 | PPL-AP-8-LC-SM

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

