

# SP-10200NNS2CABA | PLC 1X2 250UM SC/APC GRADE C OUTPUT

---



Wideband PLC Splitter, singlemode, 1x2, symmetrical split ratio, 0.250 mm cable, SC/APC grade C output

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

### Product Type

Bare splitter

## General Specifications

### Device Type

Component, rectangular

### Functionality

Splitting

### Technology Type

Planar lightwave circuit (PLC)

### Distribution Type

1 x 2 splitter

### Interface, Input

Stub tail

### Interface, Output

SC/APC

### Split Ratio

Symmetrical

### Splitter, quantity

1

## Dimensions

### Height

4 mm | 0.157 in

### Width

4 mm | 0.157 in

### Length

40 mm | 1.575 in

### Pigtail Length, Input

2.5 m | 8.202 ft

### Pigtail Length, Output

1 m | 3.281 ft

### Pigtail Diameter, Input

0.25 mm | 0.01 in

### Pigtail Diameter, Output

0.25 mm | 0.01 in

## Optical Specifications

### Fiber Type

G.657.A2

### Directivity, minimum

55 dB

# SP-10200NNS2CABA | PLC 1X2 250UM SC/APC GRADE C OUTPUT

---

<b>Polarization Dependent Loss, maximum</b>	0.2 dB
<b>Uniformity, maximum</b>	0.9 dB
<b>Wavelength Range</b>	1260–1650 nm
<b>Insertion Loss, Splitter, maximum</b>	4 dB
<b>Return Loss, Splitter, minimum</b>	50 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

