



Angle Adapter, snap-in, 3/4 in through hole (no insert included)

Product Classification

Product Type	Adapter
Product Brand	I-Line
Ordering Note	ANDREW® non-standard product

General Specifications

Adapter Type	Angle adapter
Mounting	3/4 in through hole

Dimensions

Inside Width	16.002 mm 0.63 in
Outside Width	38.1 mm 1.5 in
Inside Length	16.002 mm 0.63 in
Outside Length	46.99 mm 1.85 in
Material Thickness	2.972 mm 0.117 in

Material Specifications

Material Type	Stainless steel
---------------	-----------------

Mechanical Specifications

Installation Torque, maximum	13 ft lb 17.626 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Double stack, 1-5/8 in cable

Packaging and Weights

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in

Packaging quantity 10

Weight, gross 1.59 kg | 3.505 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant