

31768A-M



Angle Adapter, standard, M10 tapped hole

Product Classification

Product Type	Adapter
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Adapter Type	Angle adapter
Mounting	M10 tapped hole

Dimensions

Inside Width	22.352 mm 0.88 in
Outside Width	49.784 mm 1.96 in
Inside Length	22.352 mm 0.88 in
Outside Length	44.958 mm 1.77 in
Material Thickness	4.191 mm 0.165 in

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Installation Torque, maximum	15 ft lb 20.337 N-m
Installation Torque, minimum	11 ft lb 14.914 N-m
Maximum Loading	Triple stack, 1-5/8 in cable

Packaging and Weights

Height, packed	14.2 cm 5.591 in
Width, packed	14.2 cm 5.591 in
Length, packed	10.2 cm 4.016 in

31768A-M

Packaging quantity 10
Weight, gross 2.33 kg | 5.137 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system