

VSRC-MM-1550



Interlocking Channel V-Stabilizer™ for a Monopole - Adjustable from 34.5" to 57.5" Plus Vertical & Horizontal Adjustments

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity 0
Sectors, quantity 3

Dimensions

Length 1,460.5 mm | 57.5 in
Mounting Diameter, maximum 1270 mm | 50 in
Mounting Diameter, minimum 381 mm | 15 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Legs | Ring mount
Packaging quantity 1
Weight, net 162.182 kg | 357.55 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

