## **VSRC-TS-B**



Interlocking Channel V-Stabilizer™ for Tower Legs 2-8in OD- Adjustable from 34.5" to 57.5" Plus Vertical & Horizontal Adjustments

## **Product Classification**

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to

203.2 mm (8 in) OD

Pipe, quantity 0

Sectors, quantity

Tower Taper Non-tapered | Tapered

**Dimensions** 

**Length** 1,460.5 mm | 57.5 in

Mounting Diameter, maximum203.2 mm | 8 inMounting Diameter, minimum50.8 mm | 2 in

**Stand-off Distance, adjustable** 34.5–57.5 in | 87.6–146 cm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity

**Weight, net** 46.13 kg | 101.7 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted



## VSRC-TS-B

**UK-ROHS** 

Compliant/Exempted

