



2.0 mm LC/UPC Uniboot GEN 1.5, Aqua

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber connector boot

General Specifications

Boot Style	Push-pull
Color	Aqua
Ferrule Geometry	Flat

Dimensions

Compatible Cable Diameter	2 mm 0.079 in
---------------------------	-----------------

Material Specifications

Ferrule Material	Zirconia
------------------	----------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Attenuation, nominal	0.13 dB
Insertion Loss, maximum	0.15 dB
Return Loss, minimum	35 dB

Packaging and Weights

Packaging Type	Bag
----------------	-----

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

860658161

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

