

RT-NF7-2-126



High Capacity Non-Penetrating Roof Frame, 7 ft face, two 2-7/8 in OD x 126 in pipes

Product Classification

Product Type	Non-penetrating roof frame
Ordering Note	NSTD445 Compliant

General Specifications

Mounting	Non-penetrating
Pipe, quantity	2

Dimensions

Height	3,200.4 mm 126 in
Face Width	2.286 m 7.5 ft
Width	2,286 mm 90 in
Length	2.377 m 7.8 ft
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

Mechanical Specifications

Wind Rating Test Method	TIA/EIA-222
-------------------------	-------------

Packaging and Weights

Included	Ballast tray Frame Plain end pipes
----------	--

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RT-NF7-2-126

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

