RT-NF10-4-96



High Capacity Non-Penetrating Roof Frame, 10 ft face, Four 2-7/8 in OD x 96 in pipes

Product Classification	
Product Type	Non-penetrating roof frame
General Specifications	
Mounting	Non-penetrating
Pipe, quantity	4
Dimensions	
Height	2,438.4 mm 96 in
Face Width	3.2 m 10.5 ft
Width	3,200.4 mm 126 in
Length	2.377 m 7.8 ft
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in
Material Specifications	
Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included

Ballast tray | Frame | Plain end pipes (4)

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

Page 1 of 2



RT-NF10-4-96

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

Compliant

Compliant





©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025