

BTT-B8HB000000N000



BTT Tap Terminal, 8 Port, Hardened full size, butt type, 85/15 configuration, black

- Full and terminating tap versions
- Available in both butt and Inline configurations
- Available in both black and gray housing color
- Color coded ports for identification easiness

Product Classification

Regional Availability	Latin America
Product Type	Access terminal, with tap
Product Series	BTT
Minimum Order Quantity	1

General Specifications

Cable Type	No cable (stubless)
Distribution Type	8-port tap
Drop Port Type	Hardened full-size SC/APC
Drop Port, quantity	8
Enclosure Color	Black
Forward Port Type	Hardened full-size SC/APC adapter
Forward Port, quantity	1
Input Tap, quantity	1
Mounting	Handhole Pedestal Pole Strand
Port Type	Hardened full-size SC/APC
Port, quantity	10
Split Ratio	85/15
Splitter, quantity	1
Stub Type	No tail

Dimensions


Width	141 mm 5.551 in
Depth	90 mm 3.543 in

BTT-B8HB000000N000


Length 258 mm | 10.157 in

Cable Length, stub 0 ft (0 m)

Port Configuration



Ordering Tree



Ordering example

Hardened Full Tap, Black, Butt, 70/30 (BTT-B8H0D000000N000)

Material Specifications

Enclosure Material Type Glass filled polypropylene (GF-PP)

Optical Specifications

Fiber Type G.657.A2

Operating Wavelength Range 1260 – 1650 nm

Tap Drop Loss, maximum 20.79 dB

Tap Thru Loss, maximum 1.13 dB

Environmental Specifications

BTT-B8HB000000N000

Operating Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Relative Humidity	0%–100%, condensing
Environmental Space	Above ground Below ground Buried
Qualification Standards	Anatel
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

