

FGS-HTBK-12-6



FiberGuide® 12in Horizontal Tool-less Bracket Kit, 6in Tall, 4x12in

This 12 inch bracket attaches to 12 inch ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12in FiberGuide® above ladder racking.

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Support mounting kit |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|---------------------|-----------------------------|
| Color | Black |
| Note | Includes fastening hardware |
| Orientation | Horizontal |
| Section Type | Bracket |

Dimensions

| | |
|--------------------------|--------------------------------|
| Height | 195.834 mm 7.71 in |
| Width | 114.3 mm 4.5 in |
| Length | 305.664 mm 12.034 in |
| System Dimensions | 102 mm x 305 mm (4 in x 12 in) |

Material Specifications

| | |
|----------------------|-------|
| Material Type | Steel |
|----------------------|-------|

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Hardware |
| Packaging quantity | 1 |
| Weight, net | 0.953 kg 2.1 lb |

FGS-HTBK-12-6

Included Products

HDW-12021 - FiberGuide® Quick Knob with T-Bolt

HDW-12021



FiberGuide® Quick Knob with T-Bolt

Product Classification

| | |
|-------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber raceway hardware |
| Product Brand | FiberGuide® |
| Product Series | FGS |
| Minimum Order Quantity | 10 |

General Specifications

| | |
|---------------------|------------|
| Color | Black |
| Orientation | Horizontal |
| Section Type | Accessory |

Dimensions

| | |
|--------------------------|--|
| System Dimensions | 102 mm x 102 mm (4 in x 4 in) 102 mm x 152 mm (4 in x 6 in) 102 mm x 305 mm (4 in x 12 in) 102 mm x 610 mm (4 in x 24 in) 51 mm x 152 mm (2 in x 6 in) |
|--------------------------|--|

Environmental Specifications

| | |
|--------------------------------|--------------------------------|
| Flammability Rating | CSA S143 UL 2024 UL 94 V-0 |
| Halogen Characteristics | Blue Angel TCO '99 WEEE |
| Safety Standard | CSA UL |

Packaging and Weights

| | |
|---------------------------|---------------------|
| Packaging quantity | 1 |
| Weight, net | 0.015 kg 0.033 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

HDW-12021

| | |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

