# MCG23HDX-10M1296



G23HDX High Capacity 3-Sector Monopole Sector Frame,  $10.5 \text{ ft} \times 2.88$  in OD face pipes, includes twelve  $2.88 \text{ OD} \times 96$  in pipes

#### **Product Classification**

Product Type High capacity monopole sector frame

**Product Series** G2

**Ordering Note** NSTD445 Compliant

#### General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

#### **Dimensions**

Pipe Length

**Height** 2,438.4 mm | 96 in

Face Width  $3.2 \, \text{m} \, \mid \, 10.5 \, \text{ft}$ 

**Width** 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,066.8 mm | 42 in

## Material Specifications

Material Type Hot dip galvanized steel

### Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

2,438.4 mm | 96 in

Wind Rating Test Method TIA/EIA-222



# MCG23HDX-10M1296

### Packaging and Weights

Included Mounting hardware | Pipe mounts | Plain end pipes (12) | Ring mounts (2) | Sector frames

(3) | Stiff arm

Packaging quantity

# Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

