FPX-2FRH0Z480



FPX Fiber Optic Termination Panel with HMFOC tether, 2RU, 19in, Singlemode, 48 fiber, LC/APC Connector to 4x12 fiber HMFOC, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FPX

General Specifications

Functionality Patching

Body Style Symmetrical

Color Putty white

Growth Configuration Partially loaded

Interface, front LC/APC

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

Shelf Movement Sliding

Total Fibers, quantity 48

Total Ports, quantity 48

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

COMMSC PE®

FPX-2FRH0Z480

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

