

# 1065585 | FGS-HTHR-12MM-180CM



FiberGuide® Threaded Rod, 12mm Diameter, 180cm Length

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Threaded rod
Product Brand	FiberGuide®
Product Series	FGS
Warranty	One year

## General Specifications

Color	Silver
Orientation	Horizontal
Section Type	Mounting

## Dimensions

Width	12 mm   0.472 in
Length	1800 mm   70.866 in
Thread Size	12 mm
System Dimensions	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   51 mm x 152 mm (2 in x 6 in)

## Ordering Tree

# 1065585 | FGS-HTHR-12MM-180CM

	9		10
FGS - HTHR -	5/8	-	72

Rod Diameter

9	1/2	1/2 in
	5/8	5/8 in
	12 MM	12 mm
	14 MM	14 mm
	16 MM	16 mm

Rod Length

10	12	12 in
	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

\* Rod diameter and length needs to be both metric or imperial sized

## Material Specifications

**Material Type** Carbon steel

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 0.5 kg | 1.102 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

