U3XQPUCT8

Base Product



Ultra Low Loss (ULL) OM4 MPO8 (Non-Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 8-Fiber, LZSH B2ca

Product Classification

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

General Specifications

Connector A, quantity 1

Color, boot AGrayColor, connector AAquaConnector B, quantity0

Construction TypeStrandedFurcation ColorAqua

Interface, Connector A MPO-08/UPC Female

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 8

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 – 305


COMMSCOPE®

U3XQPUCT8

Cable Assembly Length Range (ft)

10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

COMMSCOPE®

U3XQPUCT8

760253116 N-008-MP-5K-F08AQ/20T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 8 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca flame rating

860659024

- MPO-08, ULTRA LOW LOSS, FEMALE, OM3/4, AQUA, 2mm

