UGGQPQXTH

Base Product



Ultra Low Loss (ULL) Singlemode MPO8 (Non-Pinned) to MPO8 (Pinned), Fiber Trunk Cable Assembly, 48-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity 6

Color, boot A Gray

Color, connector A Green

Connector B, quantity 6

Color, boot B Gray

Color, connector B Aqua

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A MPO-08/APC Female

Interface, Connector B MPO-08/APC Male

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 48

Dimensions

Breakout Length 22 in


COMMSCOPE®

UGGQPQXTH

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



UGGQPQXTH

Included Products

760245566 – Fiber indoor cable, Plenum MPO Trunk, 48 fiber multi-unit with 8 fiber subunits, Singlemode G. P-048-MP-8G1-F08YL/20T 657.A2/B2, Feet jacket marking, Yellow jacket color

860659022 – MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm 860659028 – MPO-08, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 2mm

