# UGGQXUCTN

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 192-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

#### General Specifications

Connector A, quantity 24

Color, boot A Gray

Color, connector A Green

Connector B, quantity 0

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-08/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 192

#### **Dimensions**

Breakout Length 22 in


Cable Assembly Length Range (m) 3 – 305

Cable Assembly Length Range (ft) 10 – 999

Page 1 of 3

## UGGQXUCTN

#### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

#### Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### Included Products

760248110 – Fiber indoor cable, Plenum MPO Trunk, 192 fiber multi-unit with 8 fiber subunits, Singlemode G. P-192-MP-8G1-F08YL/20T 657.A2/B2, Feet jacket marking, Yellow jacket color

Page 2 of 3



860659022

MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

