### UGGRXUC8S

#### **Base Product**



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 32-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 2

Color, boot ABlackColor, connector AGreenConnector B, quantity0

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-16/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 32

**Dimensions** 


Breakout Length22 inCable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)10 - 999

Page 1 of 3



## UGGRXUC8S

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

#### Included Products



# UGGRXUC8S

760251015 P-032-MP-8G1-F16YL

860661398

- Fiber indoor cable, Plenum MPO Trunk, 32 fiber with 16 fiber subunits,, Singlemode G.657.A2 /B2 Feet jacket marking, Yellow jacket color
- Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable

