UGVQPUCTU

Base Product



Ultra Low Loss (ULL) OM5 MPO8 (Non-Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 64-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity 8

Color, boot A Gray

Color, connector A Lime green

Connector B, quantity 0

Construction Type Stranded
Furcation Color Lime green

Interface, Connector A MPO-08/UPC Female

Interface, Connector B Unterminated

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 64

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305


Cable Assembly Length Range (ft) 10 - 999

Page 1 of 3



UGVQPUCTU

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



Included Products

760248193 P-064-MP-5G-F08AO/20T Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 64 fiber multi-unit with 8 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Aqua jacket color

Page 2 of 3



UGVQPUCTU

860659026

- MPO-08, ULTRA LOW LOSS, FEMALE, OM5, LIME-GREEN, 2mm

