## UJGQXUCTM

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 144-Fiber, Dual Rated (OFNR/LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

## General Specifications

Connector A, quantity 18

Color, boot A Gray

Color, connector A Green

Connector B, quantity

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-08/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 144

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305


COMMSC PE°

# UJGQXUCTM

#### Cable Assembly Length Range (ft)

10 - 999

## Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space**Dual Rated LSZH/Riser | Indoor

#### Regulatory Compliance/Certifications

# Agency Classification ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### Included Products

760253753 – Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 144 fiber with 2.0 mm Subunits,

Page 2 of 3

# UJGQXUCTM

N-144-MP-8G1-F08YL/20T/B2 860659022 Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

**COMMSCOPE®**