# UJGRXRX8Q

#### **Base Product**



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to MPO16 (Pinned), Fiber Trunk Cable Assembly, 128-Fiber, Dual Rated (OFNR /LSZH)

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

## General Specifications

Connector A, quantity 8

Color, boot A Black

Color, connector A Green

Connector B, quantity 8

Color, boot B Black

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A MPO-16/APC Male

Interface, Connector B MPO-16/APC Male

Jacket Color Yellow

**Polarity** Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 128

**Dimensions** 




# UJGRXRX8Q

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

# Ordering Tree



# Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



# UJGRXRX8Q



### Included Products

760251078 N-128-MP-8G1-F16YL/30T/B2 Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 128 fiber with 16-fiber 3.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, B2ca flame rating

860661398

- Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable