URVRZRZ7R

Base Product



Ultra Low Loss (ULL) OM5 MPO16 APC (Pinned) to MPO16 APC (Pinned), Fiber Array Cable Assembly, 16-Fiber, Dual Rated (OFNR/LSZH)

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity

Color, boot A Black
Color, connector A Green

Connector B, quantity 1

Color, boot BBlackColor, connector BGreenConstruction TypeStrandedFurcation ColorLime green

Interface, Connector A MPO-16/APC Male
Interface, Connector B MPO-16/APC Male

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 16

Dimensions


Cable Assembly Length Range (m) 1 - 305

COMMSCOPE°

URVRZRZ7R

Cable Assembly Length Range (ft) 1 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



Included Products

760251063 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Light Duty for MPO N-016-MP-5G-F30LM/D Patchcords, 16 fiber, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color,

Page 2 of 3

URVRZRZ7R

Dca Flame rating

860659158

 Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable