


# MCG22HDX12-4-96



G22HDX High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 12.5 ft face. Includes twelve 2 7/8in OD x 96in antenna pipes

**OBSOLETE**

This product was discontinued on: July 29, 2022

**Replaced By:**

MCG22HDX-12M-12-96    G22HDX High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 12.5ft face. Includes twelve 2 7/8in OD x 96in antenna pipes

## Product Classification

Product Type	High capacity monopole sector frame
Product Series	G2

## General Specifications

Mounting	Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity	12
Sectors, quantity	3

## Dimensions

Height	2,438.4 mm   96 in
Face Width	3.81 m   12.5 ft
Width	4,419.6 mm   174 in
Pipe Length	2,438.4 mm   96 in
Face Support Pipe Diameter	73.025 mm   2.875 in
Mounting Diameter, maximum	1270 mm   50 in
Mounting Diameter, minimum	381 mm   15 in
Pipe Outer Diameter	73.025 mm   2.875 in
Stand-off Distance	1,066.8 mm   42 in

## Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

# MCG22HDX12-4-96

---

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact your local ANDREW representative
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Pipe mounts   Plain end pipes (12)   Ring mounts (2)   Sector frames (3)   Stiff arm
<b>Packaging quantity</b>	1

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--