

# FGS-HNTS-H-12MM-A



FiberGuide® Top Support Adjustable C-Bracket Kit, 12mm for 4x24in System

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Support mounting kit
Product Brand	FiberGuide®
Product Series	FGS

## General Specifications

Product Feature	Adjustable Height
Color	Black
Orientation	Horizontal
Section Type	Bracket
Bracket Type	C-bracket
Bracket Installation Type	N/A
Attachment Type	Threaded rod

## Dimensions

Height	307.34 mm   12.1 in
Width	57.912 mm   2.28 in
Length	715.01 mm   28.15 in
Thread Size	12 mm
System Dimensions	102 mm x 610 mm (4 in x 24 in)

## Ordering Tree

# FGS-HNTS-H-12MM-A

FGS - 

HNTS

 - 

9

F

 - 

10

5/8

 - 

11

A

For Section Size

9

empty

4 x 4 in, 4 x 6 in

F

4 x 12 in

For Threaded Rod Size

10

1/2

1/2 in

1/2-LP

1/2 in, low profile

12MM

12 mm

12MM-LP

12 mm, low profile

14MM

14 mm

14MM-LP

14 mm, low profile

16MM

16 mm

16MM-LP

16 mm, low profile

5/8

5/8 in

5/8-LP

5/8 in, low profile

11

A

Adjustable

## Material Specifications

**Material Type** Carbon steel

## Packaging and Weights

**Included** Hardware

**Packaging quantity** 1

**Weight, net** 3.289 kg | 7.25 lb

Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 21, 2025

COMMScope®