# CM-30S-96



### Chain Mount Kit, 8 ft chain, includes pipe

#### **Product Classification**

Product Type Chain mount kit

### General Specifications


Chains, quantity 2
Pipe, quantity 1
Sectors, quantity 1

#### Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 2,438.4 mm | 96 in **Chain Length** 2,400.3 mm | 94.5 in Pipe Length 2,438.4 mm | 96 in Mounting Diameter, maximum 762 mm | 30 in **Mounting Diameter, minimum** 203.2 mm | 8 in **Pipe Outer Diameter** 60.96 mm | 2.4 in **Mounting Circumference, maximum** 2,392.68 mm | 94.2 in **Mounting Circumference, minimum** 635 mm | 25 in



## Outline Drawing



# Material Specifications

Material Type Hot dip galvanized steel

# Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

## Packaging and Weights

Included Chains | Plain end pipes

Packaging quantity 1

**Weight, net** 27.3 kg | 60.186 lb



# CM-30S-96

# Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

CM-30S-B – Chain Mount Base Kit, 14 in stand-off, 8 ft chain MT-651-96 – Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C

46Ksi

#### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

