

Chain Mount Base Kit, 14 in stand-off, 8 ft chain

Product Classification

Product Type Chain mount kit

General Specifications

Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 1

Dimensions

 Height
 152.4 mm | 6 in

 Width
 203.2 mm | 8 in

 Length
 203.2 mm | 8 in


 Chain Length
 2,400.3 mm | 94.5 in

Mounting Diameter, maximum762 mm | 30 inMounting Diameter, minimum203.2 mm | 8 inPipe Outer Diameter60.96 mm | 2.4 inMounting Circumference, maximum2,392.68 mm | 94.2 inMounting Circumference, minimum635 mm | 25 in



CM-30S-B

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Brackets | Chains | Hardware



CM-30S-B

Packaging quantity

Weight, net 31.8 kg | 70.107 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

1

