CM-606-B



Chain Mount Base Kit, 14 in stand-off 16 ft chain

OBSOLETE

Product Classification

Product Type Chain mount kit

General Specifications

Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 6


Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 203.2 mm | 8 in **Chain Length** 4,902.2 mm | 193 in 1524 mm | 60 in **Mounting Diameter, maximum Mounting Diameter, minimum** 355.6 mm | 14 in **Pipe Outer Diameter** 60.96 mm | 2.4 in **Mounting Circumference, maximum** 4,775.2 mm | 188 in **Mounting Circumference, minimum** 635 mm | 25 in



CM-606-B

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Brackets | Chains | Hardware

Page 2 of 3

CM-606-B

Packaging quantity

1

Weight, net 36.3 kg | 80.028 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

