

Chain Mount Kit, 16 ft chain, includes pipe

Product Classification

Product Type Chain mount kit


General Specifications

Chains, quantity 2
Pipe, quantity 2
Sectors, quantity 2

Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 2,438.4 mm | 96 in **Chain Length** 4,902.2 mm | 193 in Pipe Length 2,438.4 mm | 96 in Mounting Diameter, maximum 1524 mm | 60 in **Mounting Diameter, minimum** 203.2 mm | 8 in **Pipe Outer Diameter** 60.96 mm | 2.4 in **Mounting Circumference, maximum** 4,775.2 mm | 188 in **Mounting Circumference, minimum** 635 mm | 25 in

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Criteria One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Chains | Plain end pipes

Packaging quantity

Weight, net 53.4 kg | 117.727 lb



CM-60D-96

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

CM-60D-B – Chain Mount Base Kit, 16 ft chain

MT-651-96 – Plain End Pipe, 2-3/8 in OD x 96 in .120" A500C

46Ksi

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

