

# PROPEL-MODULES

---



Four sizes of interchangeable Propel fiber modules provide the breadth of capabilities for virtually any configuration.

- Ultra-low loss (ULL) with Method B Enhanced polarity
- Can be installed and removed from front or rear of panel
- Serialized QR code provides easy access to factory optical test results
- 8f, 12f, 16f or 24f sizes are interchangeable within Propel panels or blades

Modules support ultra-low loss OM4, OM5 wideband and singlemode fiber applications. MPO modules provide plug-and-play fiber connectivity—enabling greater flexibility, faster deployment, and easier moves, adds and changes. With 8-, 12-, 16- and 24-fiber modules and a wide range of MPO, LC and SN adapter/connector options, the Propel portfolio delivers the versatility your network demands with a minimum number of components.

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Breakout module
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## Environmental Specifications

<b>Safety Standard</b>	UL 62368
------------------------	----------