# CM-60T-B



#### Chain Mount Base Kit, 16 ft chain

#### **Product Classification**

Product Type Chain mount kit

Ordering Note ANDREW® non-standard product

**Warranty** One year

### General Specifications

**Mounting Circumference, minimum** 

Chains, quantity 2
Pipe, quantity 0
Sectors, quantity 3


#### Dimensions

Height 152.4 mm | 6 in Width 203.2 mm | 8 in Length 203.2 mm | 8 in **Chain Length** 4,902.2 mm | 193 in **Mounting Diameter, maximum** 1524 mm | 60 in **Mounting Diameter, minimum** 203.2 mm | 8 in 60.96 mm | 2.4 in **Pipe Outer Diameter Mounting Circumference, maximum** 4,775.2 mm | 188 in

635 mm | 25 in

# CM-60T-B

## Outline Drawing



### Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

**Wind Rating Criteria** One 96 in x 10 in panel antenna per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

**Included** Chains

ANDREW® an Amphenol company

# CM-60T-B

Packaging quantity

**Weight, net** 28.5 kg | 62.832 lb

1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

