

Chain Mount Base Kit, 14 in stand-off, 8 ft chain

Product Classification	
Product Type	Chain mount kit
General Specifications	
Chains, quantity	2
Pipe, quantity	0
Sectors, quantity	1
Dimensions	
Height	152.4 mm 6 in
Width	203.2 mm 8 in
Length	152.4 mm 6 in
Chain Length	2,400.3 mm 94.5 in
Mounting Diameter, maximum	762 mm 30 in
Mounting Diameter, minimum	203.2 mm 8 in
Pipe Outer Diameter	60.96 mm 2.4 in
Mounting Circumference, maximum	2,392.68 mm 94.2 in
Mounting Circumference, minimum	635 mm 25 in
Material Specifications	
Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating120 mph (BWS) at 100 ft AGLWind Rating CriteriaOne 96 in x 10 in panel antenna per sectorWind Rating Test MethodTIA/EIA-222

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

Packaging and Weights

Included	Brackets Chains Hardware
Packaging quantity	1
Weight, net	31.8 kg 70.107 lb

* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025