MC-KD14M-12-H10



Heavy Duty Double T-Arm Monopole Mount, Includes (2) Ring Mounts for 15"-50" OD Monopole, 14.5 ft x 3-1/2" OD face pipes, (12) 2-7/8" OD x 120" Antenna Pipes

Heavy Duty Double T-Arm mount design for Monopole applications featuring sturdy corner tie-backs for added stability. Includes 3-1/2" OD face pipes and (12) 2-7/8" OD Antenna Pipes.

Product Classification

Product Type

Monopole T-frame kit

General Specifications

Mounting	Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity	12
Sectors, quantity	3
Dimensions	
Height	3,048 mm 120 in
Face Width	4.42 m 14.5 ft
Width	4,419.6 mm 174 in
Pipe Length	3,048 mm 120 in
Mounting Diameter, maximum	1270 mm 50 in
Mounting Diameter, minimum	381 mm 15 in
Pipe Outer Diameter	73.025 mm 2.875 in
Stand-off Distance	1,244.6 mm 49 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	For Specifications, please contact your local

 Wind Rating
 For Specifications, please contact your local ANDREW representative

 Wind Rating Test Method
 TIA/EIA-222-G

Packaging and Weights

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

MC-KD14M-12-H10

1

Included

Pipe mounts | Plain end pipes | Ring mounts (2) | Stand-off arms

Packaging quantity

* Footnotes

Wind Rating

BWS–Base Wind Speed; FBC–Florida Building Code

Page 2 of 2

