


# UJG2XMES3

Base Product



Ultra Low Loss (ULL) Singlemode MPO24 (pinned) to MPO12 (Unpinned) Pre-terminated Trunk Cable, 2880-Fiber, 12-fiber Rollable Ribbon Central Tube, Low Smoke Zero Halogen (LSZH)/Riser

## Product Classification

Regional Availability	Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration


## General Specifications

Color, boot A	Red
Color, connector A	Green
Color, boot B	Black
Color, connector B	Green
Construction Type	Rollable ribbon
Furcation Color	Yellow
Interface, Connector A	MPO-24/APC Male
Interface, Connector B	MPO-12/APC Female
Jacket Color	Black
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	2880

## Dimensions

Cable Assembly Length Range (m)	5 – 999
Cable Assembly Length Range (ft)	15 – 999
Cable Assembly Length Range (km)	1.00 – 2.00

## Ordering Tree



## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Dual Rated LSZH/Riser

## Packaging and Weights

**Packaging Type** Wood reel

## Regulatory Compliance/Certifications

**Agency** **Classification**

ANATEL Compliant



## Included Products

# UJG2XMES3

---

760253186	–	Fiber indoor/outdoor cable, All-Dielectric, LSZH, Gel-Free, Riser Rated, Central Core Rollable
Z-2880-CN-RR-F12BK/8G1/99L		Ribbon, 2880 fiber, Singlemode G.657.A2, Feet jacket marking, Black jacket color, Cca flame
/C		rating
860638318	–	MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm
860651709	–	TeraSPEED® MPO Male 24 Fiber Connector, green, 3.6 mm