



Propel Sample Singlemode MPO-08 Distribution Module, 4 duplex LC /UPC to MPO, No fiber

- Can be installed and removed from front or rear of panel
- This component requires 2 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	Propel
Product Series	PPL

General Specifications

Functionality	Breakout
Color, front	Blue
Color, rear	Gray
Interface, front	LC/UPC
Interface Feature, front	Internal shutters
Interface, rear	MPO
Interface Feature, rear	Internal shutters
Total Fibers, quantity	0
Total Ports, quantity, front	4
Total Ports, quantity, rear	1

Dimensions

Height	11 mm   0.433 in
Width	65 mm   2.559 in
Depth	170 mm   6.693 in

Optical Specifications

Insertion Loss, maximum	dB
-------------------------	----

## Environmental Specifications

**Safety Standard** UL 62368

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

**Agency**

## Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

