

L4-DR-X

Base Product



D-CLASS LDF4-50A SureFlex® Jumper with interface types 7-16 DIN
Male Right Angle, blunt cut

Product Classification

Product Type	SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX® SureFlex®
Product Series	LDF4-50A

General Specifications

Attachment, Connector A	Factory attached
Body Style, Connector A	Right angle
Interface, Connector A	7-16 DIN Male
Specification Sheet Revision Level	B
Variable Length	For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

Dimensions

Nominal Size	1/2 in
---------------------	--------

Logo Image

L4-DR-X



Electrical Specifications

3rd Order IMD Dynamic	-119 dBm
3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB

Jumper Assembly Sample Label



Environmental Specifications

L4-DR-X

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition