RT-DF12-4-126



High Capacity DUAL Non-Penetrating Roof Frame, 12 ft face, four 2-7/8 in OD x 126 in pipes

Product Classification	
Product Type	Non-penetrating roof frame
Ordering Note	NSTD445 Compliant
General Specifications	
Mounting	Non-penetrating
Pipe, quantity	4
Dimensions	
Height	3,200.4 mm 126 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Length	2.377 m 7.8 ft
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating Test Method	TIA/EIA-222
Packaging and Weights	
Included	Ballast tray Frame Plain end pipes (4)
Regulatory Compliance/Certifications	
Agency Classification	

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

RT-DF12-4-126

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS



Below maximum concentration value Compliant as per SVHC revision on www.andrew.com/ProductCompliance Compliant Compliant

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025