# WSC-SH021210



WSC Wall Splice Cabinet for MDU applications, indoor/outdoor, for up to 48 fibers, includes 1 splice tray with heat shrink fusion, no key lock

#### Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber wall box

#### General Specifications

Functionality	Splicing
Access	Front
Cable Color	White
Cable Type	Pigtails - Stranded
Door, quantity	1
Enclosure Color	Putty white
Front Door Type	Single hinged
Interface	Splicing only
Lock Type	Locking bolt
Mounting	Wall
Splice Trays	Included
Splicing Type	Heat shrink
Dimensions	

Height	273 mm   10.748 in
Width	255 mm   10.039 in
Depth	89 mm   3.504 in

### **Environmental Specifications**

Environmental Space	Outdoor
Qualification Standards	NEMA, Type 4

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2024



## WSC-SH021210

### Packaging and Weights

Packaging quantity

uantity 1

Packaging Type Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 5, 2024

