

RT-DSF12-3-126



High Capacity DUAL Penetrating Roof Frame, 12 ft face, three 2-7/8 in OD x 126 in pipes

Product Classification

Product Type Rooftop sector frame

General Specifications

Mounting Penetrating

Pipe, quantity 3

Dimensions

Height 126 in | 3,200.4 mm

Face Width 12.5 ft | 3.81 m

Width 150 in | 3,810 mm

Length 4.3 ft | 1.311 m

Pipe Length 126 in | 3,200.4 mm

Face Support Pipe Diameter 2.88 in | 73.152 mm

Pipe Outer Diameter 2.88 in | 73.152 mm

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Frame | Plain end pipes