RT-DSF12-4-126



High Capacity DUAL Penetrating Roof Frame, 12 ft face, four 2-7/8 in OD x 126 in pipes

Product Classification	
Product Type	Rooftop sector frame
General Specifications	
Mounting	Penetrating
Pipe, quantity	4
Dimensions	
Height	3,200.4 mm 126 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Length	1.311 m 4.3 ft
Pipe Length	3,200.4 mm 126 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type

Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included

Frame | Plain end pipes

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

Classification

Below maximum concentration value

Page 1 of 2



RT-DSF12-4-126

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

Compliant

Compliant



Page 2 of 2

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

ANDREW an Amphenol company