## RT-SF10-3-96



High Capacity Penetrating Roof Frame, 10 ft face, three  $2-7/8 \text{ in OD } \times 96 \text{ in pipes}$ 

## **Product Classification**

**Product Type** Rooftop sector frame

General Specifications

**Mounting** Penetrating

Pipe, quantity 3

**Dimensions** 

**Height** 2,438.4 mm | 96 in

**Face Width** 3.2 m | 10.5 ft

**Width** 3,200.4 mm | 126 in

**Length** 1.311 m | 4.3 ft

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 73.152 mm | 2.88 in

Pipe Outer Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Frame | Plain end pipes

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value



## RT-SF10-3-96

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

