## RT-SF12-3-126



High Capacity Penetrating Roof Frame, 12 ft face, three 2-7/8 in OD x 126 in pipes

## **Product Classification**

**Product Type** Rooftop sector frame

General Specifications

**Mounting** Penetrating

Pipe, quantity 3

**Dimensions** 

**Pipe Outer Diameter** 

**Height** 3,200.4 mm | 126 in

**Face Width** 3.81 m | 12.5 ft

**Width** 3,810 mm | 150 in

**Length** 1.311 m | 4.3 ft

**Pipe Length** 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.152 mm | 2.88 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Frame | Plain end pipes

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value



73.152 mm | 2.88 in

## RT-SF12-3-126

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

