## HFT410-1SBVYF-G



HELIAX® Hybrid Cable Assembly, BiDi, 6-OVP box to RRU, UL Type TC-ER,4 power conductors 10 AWG at OVP, 2 power cords 8 AWG at RRU, 1 Simplex fiber connectors, FullAXS, PVC jacket, aluminum armor, OVP gland insert kit included

#### **Product Classification**

Regional Availability North America

Product Type Hybrid cable assembly

Product Brand HELIAX®

**Product Series** HFT

Ordering Note ANDREW® non-standard product

### General Specifications

Conductors, quantity 4

**Construction Type** Hybrid standard tail

Interface, Connector A LC

 Interface Feature, connector A
 Outdoor

 Interface Body Style, connector A
 Straight

Interface, Connector B LC

Interface Feature, connector BStandardInterface Body Style, connector BStraightJacket ColorBlack

Total Fibers, quantity

#### Dimensions

Cable Assembly Length Range (ft) 3 - 400


**Diameter Over Jacket** 18.31 mm | 0.721 in

Center Conductor Gauge 10 AWG

### Ordering Tree



## HFT410-1SBVYF-G



#### Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

**Optical Specifications** 

Fiber ModeSinglemodeFiber TypeG.657.A2

**Insertion Loss, typical note** Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

### **Environmental Specifications**

**Operating Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +75 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +167 \, ^{\circ}\text{F})$ 

Packaging and Weights

 $\textbf{Cable weight} \hspace{1.5cm} 0.5 \text{ kg/m} \hspace{0.2cm} \mid \hspace{0.2cm} 0.336 \text{ lb/ft}$ 

\* Footnotes



# HFT410-1SBVYF-G

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)