# HFT410-3SBVE-G



HELIAX® Hybrid Cable Assembly, BiDi, 6-OVP box to RRU, UL Type TC-ER, 4 power conductors 10 AWG at OVP, 1 power cord 8 AWG at RRU, 3 Simplex fiber connectors, PVC jacket, aluminum armor, OVP gland insert kit included

Grommet FA-6627-3315-GKHP is required for power cord sealing (not included)

#### **Product Classification**

Regional Availability North America

Product Type Hybrid cable assembly

Product Brand HELIAX®

Product Series HFT

Ordering Note ANDREW® non-standard product

#### General Specifications

Conductors, quantity 4

Construction Type Hybrid standard tail

Interface, Connector A LC

Interface Feature, connector AStandardInterface Body Style, connector AStraight

Interface, Connector B LC

Interface Feature, connector BStandardInterface Body Style, connector BStraightJacket ColorBlackTotal Fibers, quantity3

#### **Dimensions**

Cable Assembly Length Range (ft) 1 - 200


**Diameter Over Jacket** 18.31 mm | 0.721 in

Center Conductor Gauge 10 AWG

### Ordering Tree



## HFT410-3SBVE-G



### Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

**Optical Specifications** 

Fiber ModeSinglemodeFiber TypeG.657.A2

**Insertion Loss, typical note** Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C}$  to  $+75 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+167 \,^{\circ}\text{F}$ )

Packaging and Weights

 $\textbf{Cable weight} \hspace{1.5cm} 0.5 \, \text{kg/m} \hspace{.1cm} \mid \hspace{.1cm} 0.336 \, \text{lb/ft}$ 

\* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

