

7845389-1003 | UAP2 35LT/35HT F-DC



Carrier Access Point with MIMO 2x2 Radio Module for Low Power TDD 3500 Applications, Fiber fed, DC

OBSOLETE

Replaced By:

7845389-1036
UAP2 35LT/35HT F-DC

Carrier Access Point with MIMO 2x2 Radio Module for Low Power TDD 3500 Applications, Fiber fed, DC

Product Classification

Product Type	Access point
Product Brand	ERA®
Product Series	UAP2

General Specifications

Antenna Type	MIMO Antenna
Fan Kit	Included
Fed Type	Fiber fed
Note	CEPT CASE B compliance Detailed Product Specifications are available. Please contact your local CommScope representative. ETSI and OFCOM compliance For OFCOM compliance, the max EIRP is +24dBm for B7 (up to 27dBm for 3 carrier use case with 20+15+20 MHz)
Power Class	Low
Powering Type	External DC powered

Electrical Specifications

License Band	TDD 3500
Voltage Range	-57 to -42 Vdc

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

7845389-1003 | UAP2 35LT/35HT F-DC

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

